

CLEAN-AIR HYGIENIC COMPRESSORS

Clean-air compressors do not use oil as a lubricant and are therefore perfect for installations where clean compressed air is necessary. For surgeries, laboratories, clean rooms and other applications, Clean-air compressors provide a reliable and efficient source of compressed air to a variety of quality dependant applications.

Available as standard units or with air dryers and optional acoustic cabinets making the Clean-air range the choice of clean air professionals.

100/30S tandem

■ 6 chairs



CS30/7SCE

■ 1 chair



30/7S

■ 1 chair




50/15S

■ 3 chairs




50/15SCE

■ 3 chairs



30/7SCE

■ 1 chair



30/7SCE

■ 6 chairs



CS30/15SCE

■ 3 chairs



Model	Seats	Air Capacity		Air Capacity FAD		Motor		Voltage Volts	Noise Level dB@1m	Receiver Lt
		cfm	Lt/min	cfm	Lt/min	HP	kW			
Clean-air oil free compressors										
30/7S	1	4.5	130	3.7	105	1	0.75	230	75	30
30/15S	2	8.8	250	7.06	200	2	1.5	230	75	30
50/15S	3	8.8	250	7.06	200	2	1.5	230	75	50
100/30S TANDEM	6	17.6	500	14.12	400	2 + 2	1.5 + 1.5	230	77	100
Clean-air oil free compressors with dryer										
30/7SCE	1	4.5	130	3.7	105	1	0.75	230	75	30
30/15SCE	2	8.8	250	7.06	200	2	1.5	230	75	30
50/15SCE	3	8.8	250	7.06	200	2	1.5	230	75	50
100/30SCE TANDEM	6	17.6	500	14.12	400	2 + 2	1.5 + 1.5	230	77	100
Clean-air oil free compressors with dryer										
CS30/7S	1	4.5	130	3.7	105	1	0.75	230	63	30
CS50/15S	2	8.8	250	7.06	200	2	1.5	230	65	30
CS100/30S TANDEM	6	17.6	500	14.12	400	2 + 2	1.5 + 1.5	230	7	100
Clean-air oil free compressors with dryer in acoustic cabinet										
CS30/7SCE	1	4.5	130	3.7	105	1	0.75	230	63	30
CS30/15SCE	3	8.7	250	7.06	200	2	1.5	230	65	30
Clean-air vacuum pump & oil free compressors with dryer in acoustic cabinet										
Aspie-vacuum pump	1	81	2300	-	-	1	0.75	230	67	30
Aspir-comp 30/7SCE		4.5	130	3.7	105	1	0.75	230	67	30
Aspie-vacuum pump	3	124	3500	-	-	2	1.5	230	67	30
Aspir-comp 30/7SCE		8.7	250	7.06	200	2	1.5	230	67	30